Fillingstation Ø100 PRO with DAM2000+

Filling machines

Art. No. 110888A



Technical Data

Consists of: DANA api MATIC 2000+ Turntable **0** 100 cm Side plates and jar storage space Manual lidfitter Lid dispenser

Filling capacity: $10g - \infty g$ (honPump capacity:ca. 610 kg/houAmount of programs:20 + programsPower supply:90-305VAC 50/Power consumption:959 WSound level:Sound pressurLength:200cm

10g - ∞ g (honey) ca. 610 kg/hour 20 + programs 90-305VAC 50/60Hz 959 W Sound pressure level of the pump is <70 dB(A) 200cm

ltem#: Tarif Code: 110888A 8422 3000

Semi-automatic filling station

Our filling station PRO is an easy end-to-end solution consisting of our new and improved DANA api MATIC 2000+ with turntable, manual lidfitter and a lid dispender. It was developed to allow for an ideal workflow in order to avoid unnecessary steps and movements and to provide enough space for your packaging.

The novel design allows for the filling station to be adapted to different glas heights continuously. It comes on lockable wheels, which makes it easy to move the station around and transport it.

With this station you will be able to fill up to 400kg/880LB of honey per hour into containers starting from 10g/0,5oz. The filling precision is +/-1g.

The extra side surfaces makes it possible for a big amount of glasses to be placed for filling at the same time. This means that, as required, one or two employees can easily and efficiently carry out the entire filling and lidfitting process. Additionally, the practical storage boards make it possible to store the filled and empty glasses directly at the station, making the filling process even faster and easier.

This fillingstation comes with an integrated liddispenser and lidfitter so you only need to label your product (We also offer labelling machines). At the Apimondia trade fair in Ljubljana, the Swienty lidfitter was awarded a silver medal for its technical innovation. It is very easy to use. You take a filled glass, put the lid on. The handle is pressed down and the lid is screwed onto the glass. The torque can be set between 0-10 nm.

The lid dispenser is placed close at hand to make the work process as convenient and efficient as possible.

Propolis-etc... North American Distributor

propolis-etc.com 1-888-660-6665

