

Lid-Fitter, manual

Art. No. 110811



Swienty's manually operated lid-fitter

Simple lid fitter, usable for screwing lids and Twist-off caps, where several turns are needed to close the jar.

Operating instructions

It is very easy to use: Take a filled jar, put a cap on top and place it in the lid fitter. Push the level down, the unit starts to turn and the cap will be screwed onto the glass. The torque can be adjusted from 0.1 - 10 Nm. We recommend a torque setting of 2 - 3 Nm which is suitable for both TO and screw lids.

The lid fitter can easily be adjusted in height to fit different jar sizes.

At the Apimondia Fair in Ljubljana, the swienty Lid fitter was awarded the Silver medal for its technical innovation.

Technical Data

Dimensions:	19 x 24 x 50 cm
Jar height:	Max. 30 cm
Lid dimension:	Max. Ø8 cm
Handle:	34 cm
Weight:	10 kg
Rotational speed:	119 rotations/min.
Torque:	0.1 - 10 Nm
Power:	230 V / 50Hz (115 V / 60 Hz optional)
Power consumption:	200 W
Current:	0,9 A
Item#:	110811
Tariff code:	8422 3000
Packaging:	1 pcs / box

Propolis-etc...
North American Distributor

propolis-etc.com
1-888-660-6665



swienty
for better honey